



Hydrogen Gas Sensor H2/CT-10000

H2 Gas Sensor in Compact Housing

Key Features

• H2 monitroring in humid environments

Applications

- · Monitoring at High Humidity
- Biogas Analyzer

Measurement

Operation Principle	3-Electrode Electrochemical
Nominal Range	0 - 10000 ppm
Maximum Overload	20000 ppm
Inboard Filter	-
Output Signal	12 ± 6 nA/ppm
Resolution (Electronics dependent)	< 4.2 ppm
T90 Response Time	< 45 s
Typical Baseline Range (pure air, 20°C)	-30 ppm to 30 ppm
Maximum Zero Shift (+20°C to +40°C)	see Graph
Repeatability	< 2 % of signal
Output Linearity	Linear
Gain (Only applies to 4-Electrode sensors)	-

Rev.: Jan-21 Page 1 of 5

Phone: +41 43 311 72 00
Fax: +41 43 311 72 01
E-Mail: info@membrapor.ch
Website: www.membrapor.ch

Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland

Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





Birkenweg 2

Switzerland

Hydrogen Gas Sensor H2/CT-10000

Electrical

Rec. Load Resistor	10 - 33 Ω
Bias (V_Sens-V_Ref)	not recommended
Conformity to RoHS directive	RoHS Compliance

Environmental

Relative Humidity Range	50 % to 95 % RH non-condensing
Temperature Range	-40 °C to 50 °C
Pressure Range	Atmospheric ± 10%
Pressure Coefficient	N.D.
Humidity Effect	None

Lifetime

Expected Operation Life	2 years in air
Expected Long Term Output Drift in air	< 2 % signal loss per month after stabilization
Filter Life	
Storage Life	6 months in container
Rec. Storage Temperature	5°C - 20°C
Warranty Period	12 months from date of dispatch

Rev.: Jan-21 Page 2 of 5

Phone: +41 43 311 72 00 Membrapor AG Fax: +41 43 311 72 01 E-Mail: info@membrapor.ch CH-8304 Wallisellen Website: www.membrapor.ch


Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





Hydrogen Gas Sensor H2/CT-10000

Compact-Size Outline Dimensions



Mechanical

Weight 13 g

Orientation Any

Housing material Polycarbonate

Rev.: Jan-21 Page 3 of 5

Phone: +41 43 311 72 00

Fax: +41 43 311 72 01

E-Mail: info@membrapor.ch

Website: www.membrapor.ch

Switzerland

Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





Hydrogen Gas Sensor H2/CT-10000

Cross Sensitivity Data

The table below does not claim to be complete. Interfering gases should not be used for calibration. Please contact Membrapor AG for further support regarding cross sensitivities.

Interfering Gas Cross-Sens. [%]

CO < 100

Important Application Notes

H2 sensors lose >10% of their initial sensitivity within the first month after production before the output stabilizes.

Rev.: Jan-21 Page 4 of 5

Phone: +41 43 311 72 00
Fax: +41 43 311 72 01
E-Mail: info@membrapor.ch
Website: www.membrapor.ch

Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland

Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar








Hydrogen Gas Sensor H2/CT-10000

Temperature dependence

The output of an electrochemical sensor varies with temperature. The graphs below show the temperature-dependent variation of baseline and sensitivity, respectively. The results shown here are raw data (batch average) without any post-processing steps. The sensitivity and baseline are referenced to the signal at 20°C (reference point).

Please note: It is highly recommended to acquire the temperature dependence curves with the whole instrument. The sampling system, the humidity, the electronics and the interaction between the electronics and the sensor have a significant impact on the temperature dependence of the final measurement reading.



Baseline shifted with respect to reference point at 20°C.

Rev.: Jan-21 Page 5 of 5

Phone: +41 43 311 72 00 Fax: +41 43 311 72 01 E-Mail: info@membrapor.ch Website: www.membrapor.ch Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland

Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar